


Personal Floor Scale KERN MPE · MPE-E



High quality personal floor scale with BMI function – with approval for professional medical use in medical diagnostics, verification optional



KERN MPE-H



KERN MPE-P

Personal Floor Scale KERN MPE · MPE-E



Features

- Verification class III (verification is optional)
- Approved as a medical device according to 93/42/EEC or regulation (EU) 2017/745
- **1** Practical second display on the back of the scale, which makes it easy for both the patient and the doctor or nursing staff to read the weight
- **2** The MPE-HM model has an elegant height rod integrated into the column, which can be pulled out for use and has a sturdy plastic head rest and a measuring range from 90-205 cm
- The ergonomically optimised shape and robust design mean that this range is ideal for daily use in a professional environment
- Secure and non-slip positioning with height-adjustable rubber feet
- Level indicator to level the balance precisely
- Large platform with non-slip and wear-resistant surface made of plastic, to provide a secure footing for patients
- Hold function: While weighing patients that are unable to stand still, a mean average weight value is determined. This allows for sufficient time to attend to the patient, and then get a weight reading
- Mother and child function: the parent's weight is measured, and the scale is reset to zero via the button. Subsequently, the parent and baby are weighed together. The weight of the child will then show on the display. This is particularly practical for weighing infants, who can remain cradled in the arms of a parent during the weighing process
- BMI function to determine underweight/normal weight/surplus weight
- High resolution readability: readability [d] can be increased by one decimal place for 5 sec. by the touch of a key
- Data interface RS-232 as standard

- **3** Easy to transport thanks to the two integrated transport wheels
- Battery- or mains-powered, rechargeable battery operation optional
- Protective working cover included with delivery
- KERN MPE-E: Identical in construction to KERN MPE, but supplied without mains adapter. Batteries included in the scope of delivery and therefore particularly attractive in price

Technical data

- Large backlit LCD display, digit height 25 mm
- Weighing plate dimensions W×D×H
365×360×80 mm
- Overall dimensions W×D×H
MPE-PM: 365×570×1030 mm
MPE-HM: 365×570×2134 mm, with extracted height rod
- Net weight approx. 12 kg

KERN MPE

- Battery operation possible, 6×1.5 V AA not included, operating time up to 20 h
- Mains adapter external, standard


KERN MPE-E

- Battery operation, 6×1.5 V AA standard, operating time up to 20 h


Accessories

- Protective working cover over the display device, scope of delivery: 5 items, KERN MPE-A01S05
- Cleaning cloths, alcohol-free cloths for disinfectant wiping, quick acting, based on modern quaternary ammonium compounds and effective against papova viruses. Particularly gentle on materials, and very well suited for disinfecting products which are sensitive to alcohol. Fulfill the legal requirements for occupational safety in accordance with TRGS 525/540. Packaging contents 100 pcs., size 20×22 cm per cloth, KERN MYC-01
- Internal rechargeable battery pack, operating time up to 40 h without backlight, charging time approx. 12 h, KERN MBC-A08
- External mains adapter, 100 V - 240 V, Standard EU, CH, UK, KERN YKA-43
- External mains adapter, 100 V - 240 V, Standard EU, KERN YKA-44
- Interface cable RS-232 to connect an external device, KERN CFS-A01
- Matrix needle printer, KERN YKN-01
- Affordable universal label printer to print out weights on thermal labels. ASCII-capable. Convenient Auto-Forward function to automatically jump from label to label (only with KERN standard labels), KERN YKE-01
- Thermal printer, KERN YKB-01N
- For further details, plenty of further accessories and suitable printers, see Internet

STANDARD



OPTION



FACTORY



Model	Weighing range		Readout	Verification value	Mandatory by law
	[Max]	[d]			
KERN		kg	kg	kg	KERN
MPE 200K-1PEM	250	0,1	0,1	0,1	965-129
MPE 250K100PM	250	0,1	0,1	0,1	965-129
MPE 200K-1HEM	250	0,1	0,1	0,1	965-129
MPE 250K100HM	250	0,1	0,1	0,1	965-129

*Within the EU, official verification (conformity assessment according to NAWI 2014/31/EU) is mandatory by law for scales that are intended for use as a medical device. Please add this to your order. We require the location of use and the post code for the verification

CAL EXT
Adjusting program CAL
 For quick setting up of the balance's accuracy. External adjusting weight required

MEMORY
Memory
 Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.

RS 232
Data interface RS-232
 To connect the balance to a printer, PC or network

RS 485
RS-485 data interface
 To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible

USB
USB data interface
 To connect the balance to a printer, PC or other peripherals

BT
Bluetooth* data interface
 To transfer data from the balance to a printer, PC or other peripherals

WIFI
WIFI data interface
 To transfer data from the balance to a printer, PC or other peripherals

SWITCH
Control outputs (optocoupler, digital I/O)
 To connect relays, signal lamps, valves, etc.

STATISTIC
Statistics
 Using the saved values, the device calculates statistical data, such as average value, standard deviation etc.

SOFTWARE
PC Software
 to transfer the measurements from the device to a PC

GLP INTERN
GLP/ISO log internal
 The balance displays weight, date and time, independent

GLP PRINTER
GLP/ISO log
 With date and time. Only with KERN printers

KCP PROTOCOL
KERN Communication Protocol (KCP)
 It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems

PCS
Piece counting
 Reference quantities selectable. Display can be switched from piece to weight

SUM
Totalising level A
 The weights of similar items can be added together and the total can be printed out

UNIT
Weighing units
 Can be switched to e.g. nonmetric units. Please refer to website for more details

TOL
Weighing with tolerance range (Check weighing)
 Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model

ZERO
ZERO
 Resets the display to "0"

MOVE
Hold function
 When patients do not stand, sit or lie completely still, a stable weight is calculated using an average weight

MOVE
Hold function
 When the weighing conditions are unstable, a stable weight is calculated as an average value

IP
Protection against dust and water splashes IPxx
 The type of protection is shown in the pictogram of. DIN EN 60529:2000-09, IEC0529:1989+A1:1999 +A2:2013

UNDER
Suspended weighing
 Load support with hook on the underside of the balance

BATT
Battery operation
 Ready for battery operation. The battery type is specified for each device

RECHARGE
Battery operation rechargeable
 Prepared for a rechargeable battery operation

ACCU
Rechargeable battery pack
 Rechargeable set

MULTI
Universal plug-in power supply
 with universal input and optional input socket adapters for
 A) EU, CH
 B) EU, CH, GB, US
 C) EU, CH, GB, US, AUS

230 V
Plug-in power supply
 230V/50Hz in standard version for EU. On request GB, AUS or US version available

230 V
Integrated power supply unit
 Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, AUS or US on request

DMS
Weighing principle Strain gauges
 Electrical resistor on an elastic deforming body

PEAK
Peak hold function
 capturing a peak value within a measuring process

PUSH/PULL
Push and Pull
 the measuring device can capture tension and compression forces

SCALE
Integrated scale
 In the eyepiece

360°
360° rotatable microscope head

360°
Monocular Microscope
 For the inspection with one eye

BINDO
Binocular Microscope
 For the inspection with both eyes

TRINO
Trinocular Microscope
 For the inspection with both eyes and the additional option for the connection of a camera

ABBE
Abbe Condenser
 With high numerical aperture for the concentration and the focusing of light

HAL
Halogen illumination
 For pictures bright and rich in contrast

LED
LED illumination
 Cold, energy-saving and especially long-life illumination

FL-HBD
Fluorescence illumination for compound microscopes
 With 100 W mercury lamp and filter

FL-LED
Fluorescence illumination for compound microscopes
 With 3 W LED illumination and filter

PH
Phase contrast unit
 For a higher contrast

DF
Darkfield condenser/unit
 For a higher contrast due to indirect illumination

POLAR
Polarising unit
 To polarise the light

INFINITY
Infinity system
 Infinity corrected optical system

AUTO ATC
Automatic temperature compensation
 For measurements between 10 °C and 30 °C

M +3 DAYS
Conformity assessment
 The time required for conformity assessment is specified in the pictogram

1 DAY
Package shipment
 The time required for internal shipping preparations is shown in days in the pictogram

2 DAYS
Pallet shipment
 The time required for internal shipping preparations is shown in days in the pictogram

*The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Other trademarks and trade names are those of their respective owners.