

Personal Floor Scale KERN MPN-P · MPN-H



**Integratable personal scales for wireless transfer of weighing data to EMR or EHR systems**



KERN MPN-H

KERN MPN-P

## Personal Floor Scale KERN MPN-P · MPN-H



### Features

- Verification class III (verification is optional)
- Approved as a medical device according to 93/42/EEC or regulation (EU) 2017/745
- Thanks to the integrated WiFi interface, this model is suited for wireless transfer of weights directly into the digital patient records. By doing this, any documentation or transfer errors which occur during manual data transfer are eliminated. Thanks to this technology, this model can be integrated into existing or future EMR and EHR systems and ensures that your investment is future-proofed right now
- KERN Universal Port (KUP): permits the connection of an external KUP interface adapter, such as, for example, RS-232, USB, Bluetooth, WiFi or Ethernet, for the exchange of data and control commands, without any installation outlay
- **1** Practical second display on the back of the scale, which makes it easy for both the patient and the doctor or nursing staff to read the weight
- **2** The MPN-HM model has an elegant height rod integrated into the column, which can be pulled out for use and has a sturdy plastic head rest and a measuring range from 89 - 205 cm
- **3** Patients with a height below 80 cm can be measured using the measuring scale fitted on the column
- The ergonomically optimised shape and robust design mean that this range is ideal for daily use in a professional environment

- Secure and non-slip positioning with height-adjustable rubber feet
- Large platform with non-slip and wear-resistant surface made of plastic, to provide a secure footing for patients
- Hold function: While weighing patients that are unable to stand still, a mean average weight value is determined. This allows for sufficient time to attend to the patient, and then get a weight reading
- Mother and child function: the parent's weight is measured, and the scale is reset to zero via the button. Subsequently, the parent and baby are weighed together. The weight of the child will then show on the display. This is particularly practical for weighing infants, who can remain cradled in the arms of a parent during the weighing process
- BMI function to determine underweight/normal weight/surplus weight
- High resolution readability: readability [d] can be increased by one decimal place for 5 sec. by the touch of a key
- **4** Battery- or mains-powered, rechargeable battery operation optional
- **5** Easy to transport thanks to the two integrated transport wheels
- Protective working cover included with delivery

### Technical data

- Large LCD display, digit height 25 mm
- Weighing plate dimensions W×D×H 365×360×80 mm
- Battery operation possible, 6×1.5 V AA not included, operating time up to 20 h
- Mains adapter external, standard
- Net weight approx. 12 kg


### Accessories

- Internal rechargeable battery pack, operating time up to 48 h, charging time approx. 8 h, KERN YMR-01
- External mains adapter, 100 V - 240 V, Standard EU, UK, KERN YKA-51
- External data interface RS-232, interface cable included, KERN KUP-01
- External data interface USB, interface cable included, KERN KUP-03
- External data interface Ethernet, KERN KUP-04
- Bluetooth interface adapter, KERN KUP-06
- Extension box for connecting up to three interfaces in parallel, KERN KUP-13
- Memory module with real time clock (alibi memory), KERN YMM-03

#### STANDARD



#### OPTION



#### FACTORY



\*Within the EU, official verification (conformity assessment according to NAWI 2014/31/EU) is mandatory by law for scales that are intended for use as a medical device. Please add this to your order. We require the location of use and the post code for the verification

Model	Weighing range	Readout	Verification value	Overall dimensions (with extracted height rod)	Mandatory by law
	[Max] kg	[d] kg	[e] kg	W×D×H mm	<b>Verification</b>
KERN					<b>M00</b> KERN
MPN 200K-1PM	250	0,1	0,1	365×570×1030	965-129
MPN 200K-1HM	250	0,1	0,1	365×570×2134	965-129

**CAL EXT**  
**Adjusting program CAL**  
 For quick setting up of the balance's accuracy. External adjusting weight required

**MEMORY**  
**Memory**  
 Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.

**RS 232**  
**Data interface RS-232**  
 To connect the balance to a printer, PC or network

**RS 485**  
**RS-485 data interface**  
 To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible

**USB**  
**USB data interface**  
 To connect the balance to a printer, PC or other peripherals

**BT**  
**Bluetooth\* data interface**  
 To transfer data from the balance to a printer, PC or other peripherals

**WIFI**  
**WIFI data interface**  
 To transfer data from the balance to a printer, PC or other peripherals

**SWITCH**  
**Control outputs (optocoupler, digital I/O)**  
 To connect relays, signal lamps, valves, etc.

**STATISTIC**  
**Statistics**  
 Using the saved values, the device calculates statistical data, such as average value, standard deviation etc.

**SOFTWARE**  
**PC Software**  
 to transfer the measurements from the device to a PC

**GLP INTERN**  
**GLP/ISO log internal**  
 The balance displays weight, date and time, independent

**GLP PRINTER**  
**GLP/ISO log**  
 With date and time. Only with KERN printers

**KCP PROTOCOL**  
**KERN Communication Protocol (KCP)**  
 It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems

**PCS**  
**Piece counting**  
 Reference quantities selectable. Display can be switched from piece to weight

**SUM**  
**Totalising level A**  
 The weights of similar items can be added together and the total can be printed out

**UNIT**  
**Weighing units**  
 Can be switched to e.g. nonmetric units. Please refer to website for more details

**TOL**  
**Weighing with tolerance range** (Check weighing)  
 Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model

**ZERO**  
**ZERO**  
 Resets the display to "0"

**MOVE**  
**Hold function**  
 When patients do not stand, sit or lie completely still, a stable weight is calculated using an average weight

**MOVE**  
**Hold function**  
 When the weighing conditions are unstable, a stable weight is calculated as an average value

**IP**  
**Protection against dust and water splashes IPxx**  
 The type of protection is shown in the pictogram of. DIN EN 60529:2000-09, IEC0529:1989+A1:1999 +A2:2013

**UNDER**  
**Suspended weighing**  
 Load support with hook on the underside of the balance

**BATT**  
**Battery operation**  
 Ready for battery operation. The battery type is specified for each device

**RECHARGE**  
**Battery operation rechargeable**  
 Prepared for a rechargeable battery operation

**ACCU**  
**Rechargeable battery pack**  
 Rechargeable set

**MULTI**  
**Universal plug-in power supply**  
 with universal input and optional input socket adapters for  
 A) EU, CH  
 B) EU, CH, GB, US  
 C) EU, CH, GB, US, AUS

**230 V**  
**Plug-in power supply**  
 230V/50Hz in standard version for EU. On request GB, AUS or US version available

**230 V**  
**Integrated power supply unit**  
 Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, AUS or US on request

**DMS**  
**Weighing principle Strain gauges**  
 Electrical resistor on an elastic deforming body

**PEAK**  
**Peak hold function**  
 capturing a peak value within a measuring process

**PUSH/PULL**  
**Push and Pull**  
 the measuring device can capture tension and compression forces

**SCALE**  
**Integrated scale**  
 In the eyepiece

**360°**  
**360° rotatable microscope head**

**360°**  
**Monocular Microscope**  
 For the inspection with one eye

**BINDO**  
**Binocular Microscope**  
 For the inspection with both eyes

**TRINO**  
**Trinocular Microscope**  
 For the inspection with both eyes and the additional option for the connection of a camera

**ABBE**  
**Abbe Condenser**  
 With high numerical aperture for the concentration and the focusing of light

**HAL**  
**Halogen illumination**  
 For pictures bright and rich in contrast

**LED**  
**LED illumination**  
 Cold, energy-saving and especially long-life illumination

**FL-HBD**  
**Fluorescence illumination for compound microscopes**  
 With 100 W mercury lamp and filter

**FL-LED**  
**Fluorescence illumination for compound microscopes**  
 With 3 W LED illumination and filter

**PH**  
**Phase contrast unit**  
 For a higher contrast

**DF**  
**Darkfield condenser/unit**  
 For a higher contrast due to indirect illumination

**POLAR**  
**Polarising unit**  
 To polarise the light

**INFINITY**  
**Infinity system**  
 Infinity corrected optical system

**AUTO ATC**  
**Automatic temperature compensation**  
 For measurements between 10 °C and 30 °C

**M +3 DAYS**  
**Conformity assessment**  
 The time required for conformity assessment is specified in the pictogram

**1 DAY**  
**Package shipment**  
 The time required for internal shipping preparations is shown in days in the pictogram

**2 DAYS**  
**Pallet shipment**  
 The time required for internal shipping preparations is shown in days in the pictogram

\*The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Other trademarks and trade names are those of their respective owners.