



Mounted phase contrast condenser



Simple PH condenser with 40× PH slide



Lab Line

High-quality phase contrast microscope – specially pre-configured with a series of options for flexible expansion

Features

- We have developed this series specially for general applications with phase contrast method. In addition, the stable, modular construction system of the OBL series offers many more options
- Depending on the application, there is a choice of models with strong, infinitely dimmable 3W LED or 20W halogen illumination (Philips)
- A special fixed, pre-centred phase contrast condenser as well as field diaphragm give you a simplified Koehler illumination and thereby a powerful phase-contrast display of your sample
- The large mechanical stage and its specimen holder holds up to two samples at the same time and is quick and easy to focus using a coaxial coarse and fine focusing knob on both sides
- A large selection of eyepieces, objectives and colour filters, a simple polarising unit as well as further phase contrast units are available to you as accessories

- A protective dust cover, eye cups, as well as multi-lingual user instructions are included in the scope of delivery
- A C-mount adapter is required to connect a camera to the trinocular version. You can select this adapter from the following model outfit list
- Please find detailed information in the following model outfit list

Scope of application

- Haematology, urology, gynaecology, dermatology, pathology, microbiology and parasitology, immunology, Sewage treatment plants, Oncology, entomology, vets, water analysis and breweries

Applications/Samples

- Specially for extremely translucent, thin, low-contrast, challenging samples (e.g. living mammal cells, bacteria, tissue) with phase contrast

Technical data

- Infinity optical system
- Quadplex nosepiece
- Siedentopf 30° inclined/360° rotatable
- Diopter adjustment: One-sided
- Overall dimensions W×D×H 395×200×380 mm
- Net weight approx. 6,7 kg

STANDARD



OPTION



Model

Standard configuration

KERN	Tube	Eyepiece	Objective quality	Objectives	Illumination
OBL 146	Binocular	HWF 10×/ø 20 mm	Infinity E-Plan/Plan		3 W LED (transmitted)
OBL 155	Trinocular	HWF 10×/ø 20 mm	Infinity E-Plan/Plan	4×/PH10×/PH40×/100×	20 W Halogen (transmitted)
OBL 156	Trinocular	HWF 10×/ø 20 mm	Infinity E-Plan/Plan		3 W LED (transmitted)

Model outfit		Model KERN			Order number
		OBL 155	OBL 146	OBL 156	
Eyepieces (23,2 mm)	HWF 10×/∅ 20 mm	✓✓	✓✓	✓✓	OBB-A1404
	WF 16×/∅ 13 mm	○○	○○	○○	OBB-A1354
	HWF 10×/∅ 20 mm (with Pointer)	○	○	○	OBB-A1448
Infinity E-Plan objectives	4×/0,11 W.D. 12,1 mm	✓	✓	✓	OBB-A1161
	10×/0,25 W.D. 2,1 mm	○	○	○	OBB-A1159
	40×/0,65 (spring-loaded) W.D. 0,58 mm	○	○	○	OBB-A1160
	100×/1,25 (oil) (spring-loaded) W.D. 0,19 mm	✓	✓	✓	OBB-A1158
	Plan 20×/0,40 (spring-loaded) W.D. 2,41 mm	○	○	○	OBB-A1250
	Plan 60×/0,80 (spring-loaded) W.D. 0,33 mm	○	○	○	OBB-A1270
	Plan 100×/1,15 (water) (spring-loaded) W.D. 0,18 mm	○	○	○	OBB-A1437
Binocular tube	<ul style="list-style-type: none"> • Butterfly 30° inclined/360° rotatable • Interpupillary distance 50 – 75 mm (for infinity system) • Diopter adjustment: One-sided 	○	✓	○	OBB-A1578
Trinocular tube	<ul style="list-style-type: none"> • Butterfly 30° inclined/360° rotatable • Interpupillary distance 50 – 75 mm • Light distribution 20:80 (for infinity system) • Diopter adjustment: One-sided 	✓	○	✓	OBB-A1582
Mechanical stage	<ul style="list-style-type: none"> • Stage size W×D 145×130 mm • Travel 76×52 mm • Coaxial coarse and fine focusing knobs, scale: 2 µm • Two slide holder 	✓	✓	✓	
PH condenser	Abbe N.A. 1,25 precentered, for bright field and phase contrast	✓	✓	✓	OBB-A1398
	Infinity PH-Plan objective 10×	✓	✓	✓	OBB-A1390
	Infinity PH-Plan objective 20×	○	○	○	OBB-A1391
	Infinity PH-Plan objective 40×	✓	✓	✓	OBB-A1392
	Infinity PH-Plan objective 100×	○	○	○	OBB-A1393
Phase contrast units	PH slide 10×	✓	✓	✓	OBB-A1399
	PH slide 20×	○	○	○	OBB-A1400
	PH slide 40×	✓	✓	✓	OBB-A1401
	PH slide 100×	○	○	○	OBB-A1402
	Centering eyepiece	✓	✓	✓	
Darkfield condenser	N.A. 0,85 – 0,91 (dry, paraboloid)	○	○	○	OBB-A1422
Illumination	20 W Halogen spare bulb (transmitted)	✓			OBB-A1643
	3 W LED illumination system (transmitted) (non-rechargeable)		✓	✓	
Colour filters for transmitted illumination	Blue (built-in)	✓	✓	✓	
	Green	✓	✓	✓	OBB-A1188
	Yellow	○	○	○	OBB-A1165
	Grey	○	○	○	OBB-A1183
C-Mount	0,5× (focus adjustable)	○		○	OBB-A1515
	1×	○		○	OBB-A1514

For further optional accessories, please see the list of items for the OBL-12 and OBL-13 series from page 17

✓ = Included with delivery

○ = Option

360° rotatable microscope head	Fluorescence illumination for compound microscopes With 100 W mercury lamp and filter	Integrated scale In the eyepiece	Battery operation Ready for battery operation. The battery type is specified for each device.
Monocular Microscope For the inspection with one eye	Fluorescence illumination for compound microscopes With 3 W LED illumination and filter	SD card For data storage	Battery operation rechargeable Prepared for a rechargeable battery operation
Binocular Microscope For the inspection with both eyes	Phase contrast unit For a higher contrast	USB 2.0 interface For data transmission	Plug-in power supply 230V/50Hz in standard version for EU. On request GB, AUS or USA version.
Trinocular Microscope For the inspection with both eyes and the additional option for the connection of a camera	Darkfield condenser/unit For a higher contrast due to indirect illumination	USB 3.0 interface For data transmission	Integrated power supply unit Integrated in microscope. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.
Abbe Condenser With high numerical aperture for the concentration and the focusing of light	Polarising unit To polarise the light	WIFI data interface: For transmitting of the picture to a mobile display device	Package shipment The time required to manufacture the product internally is shown in days in the pictogram.
Halogen illumination For pictures bright and rich in contrast	Infinity system Infinity corrected optical system	HDMI digital camera For direct transmitting of the picture to a display device	Pallet shipment The time required to manufacture the product internally is shown in days in the pictogram.
LED illumination Cold, energy-saving and especially long-life illumination	Zoom magnification For stereomicroscopes	PC software To transfer the measurements from the device to a PC.	
Incident illumination For non-transparent objects	Auto-focus For automatic control of the focus level	Automatic temperature compensation For measurements between 10 °C and 30 °C	
Transmitting illumination For transparent objects	Parallel optical system For stereomicroscopes, enables fatigue-proof working	Protection against dust and water splashes IPxx: The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013	
Fluorescence illumination For stereomicroscopes			

Abbreviations

C-Mount	Adapter for the connection of a camera to a trinocular microscope	SLR camera	Single-Lens Reflex camera
FPS	Frames per second	SWF	Super Wide Field (Field number at least \varnothing 23 mm for 10 \times eyepiece)
H(S)WF	High (Super) Wide Field (Eyepiece with high eye point for wearers of glasses)	W.D.	Working Distance
LWD	Long Working Distance	WF	Wide Field (Field number up to \varnothing 22 mm for 10 \times eyepiece)
N.A.	Numerical Aperture		