

Digital Refractometer KERN ORL-B



Transport and storage case



Rear view, screw-on battery compartment cover

## Digital refractive index measurement for laboratories and the industry for multi-application ► Laboratory refractometer

### Features

- The models in the KERN ORL range are accurate, universal and maintenance-free digital desktop refractometers
- Other key features are the extra-large measuring range and a high degree of accuracy
- With their handy design, they are ideal for convenient and rapid everyday use
- The large, easy-to-read multi-function display with integrated temperature display supports the user to reliably determine the measurement
- The integrated automatic temperature compensation (ATC), avoids the manual conversion of the measurement. This allows a quick and efficient usage of the instrument

- Rapid, user-friendly calibration of the refractometer is possible at any time using standard commercial distilled water
- Mean value measurement (15 measurements)
- The following accessory-parts are included:
  - Pipette
  - Storage box
  - USB cable
  - Power adapter
  - Screwdriver


### Technical data

- Measurement temperature: 0 °C – 40 °C
- Overall dimensions W×D×H 180×100×55 mm
- Net weight approx. 365 g (without battery)
- Power supply: USB connection, as an alternative 1 × battery 3.7 V 3000 mA (not included with delivery)
- ATC (Automatic Temperature Compensation)
- Minimum sample volume: 0,3–0,4 ml
- Automatic energy management (AUTO-OFF after 3 Minutes)
- Mean value measurement (15 measurements)

### Accessories

- Rechargeable Battery 3,7 V 3000 mA, KERN ORL-A2007
- ORA-A1010 Calibration liquid

! Also available with calibration certificate, see page 108!



Model	Scales	Measuring range	Accuracy	Division
<b>KERN</b>				
ORL 94BS	Brix Refractive index	0 – 94 % 1,3330 – 1,5290 nD	± 0,1 % ± 0,0002 nD	0,1 % 0,0001 nD

<b>360° rotatable microscope head</b>	<b>Fluorescence illumination for compound microscopes</b> With 100 W mercury lamp and filter	<b>Integrated scale</b> In the eyepiece	<b>Battery operation</b> Ready for battery operation. The battery type is specified for each device.
<b>Monocular Microscope</b> For the inspection with one eye	<b>Fluorescence illumination for compound microscopes</b> With 3 W LED illumination and filter	<b>SD card</b> For data storage	<b>Battery operation rechargeable</b> Prepared for a rechargeable battery operation
<b>Binocular Microscope</b> For the inspection with both eyes	<b>Phase contrast unit</b> For a higher contrast	<b>USB 2.0 interface</b> For data transmission	<b>Plug-in power supply</b> 230V/50Hz in standard version for EU. On request GB, AUS or USA version.
<b>Trinocular Microscope</b> For the inspection with both eyes and the additional option for the connection of a camera	<b>Darkfield condenser/unit</b> For a higher contrast due to indirect illumination	<b>USB 3.0 interface</b> For data transmission	<b>Integrated power supply unit</b> Integrated in microscope. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.
<b>Abbe Condenser</b> With high numerical aperture for the concentration and the focusing of light	<b>Polarising unit</b> To polarise the light	<b>WIFI data interface:</b> For transmitting of the picture to a mobile display device	<b>Package shipment</b> The time required to manufacture the product internally is shown in days in the pictogram.
<b>Halogen illumination</b> For pictures bright and rich in contrast	<b>Infinity system</b> Infinity corrected optical system	<b>HDMI digital camera</b> For direct transmitting of the picture to a display device	<b>Pallet shipment</b> The time required to manufacture the product internally is shown in days in the pictogram.
<b>LED illumination</b> Cold, energy-saving and especially long-life illumination	<b>Zoom magnification</b> For stereomicroscopes	<b>PC software</b> To transfer the measurements from the device to a PC.	
<b>Incident illumination</b> For non-transparent objects	<b>Auto-focus</b> For automatic control of the focus level	<b>Automatic temperature compensation</b> For measurements between 10 °C and 30 °C	
<b>Transmitting illumination</b> For transparent objects	<b>Parallel optical system</b> For stereomicroscopes, enables fatigue-proof working	<b>Protection against dust and water splashes IPxx:</b> The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013	
<b>Fluorescence illumination</b> For stereomicroscopes			

## Abbreviations

<b>C-Mount</b>	Adapter for the connection of a camera to a trinocular microscope	<b>SLR camera</b>	Single-Lens Reflex camera
<b>FPS</b>	Frames per second	<b>SWF</b>	Super Wide Field (Field number at least $\varnothing$ 23 mm for 10 $\times$ eyepiece)
<b>H(S)WF</b>	High (Super) Wide Field (Eyepiece with high eye point for wearers of glasses)	<b>W.D.</b>	Working Distance
<b>LWD</b>	Long Working Distance	<b>WF</b>	Wide Field (Field number up to $\varnothing$ 22 mm for 10 $\times$ eyepiece)
<b>N.A.</b>	Numerical Aperture		